

## Torque screwdriver - TSD-M 1,2NM - 1212224

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm

### Product Features

- High-precision, finely adjustable torque screwdrivers according to EN ISO 6789
- Torque screwdrivers with hexagonal fast connection holder
- TSD-M ... torque screwdrivers are adjustable from 0.3 - 6.0 Nm

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	180.0 g
Custom tariff number	82054000
Country of origin	Czech Republic

### Technical data

#### Dimensions

Length (b)	150 mm
Width (a)	36.5 mm
Height	36.5 mm

#### General

Color	black
-------	-------

### Classifications

#### eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401

# Torque screwdriver - TSD-M 1,2NM - 1212224

## Classifications

### eCl@ss

eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040222

### ETIM

ETIM 2.0	EC000158
ETIM 3.0	EC000158
ETIM 4.0	EC002132
ETIM 5.0	EC002132

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

---