

## Replacement die - CF 500/DIE RC 10 - 1212244


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die for crimping machine CF 500, for cable lugs (C-RC... and C-FC...) 0.5 ... 10 mm<sup>2</sup>



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 450027
GTIN	4046356450027
Weight per Piece (excluding packing)	66.800 g
Custom tariff number	84799070
Country of origin	Germany

### Technical data

#### Dimensions

Cable diameter	0.9 mm ... 3.7 mm
----------------	-------------------

#### General

Compression	Indent crimp
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>
Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	10 mm <sup>2</sup>

# Replacement die - CF 500/DIE RC 10 - 1212244

## Classifications

### eCl@ss

eCl@ss 10.0.1	17139201
eCl@ss 4.0	21043000
eCl@ss 4.1	21043000
eCl@ss 5.0	21059000
eCl@ss 5.1	21059000
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 8.0	21049090
eCl@ss 9.0	17139201

### ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 5.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

## Replacement die - CF 500/DIE RC 10 - 1212244

### Approvals

#### Approval details

EAC		RU C- DE.AI30.B.01549
-----	---	--------------------------