

## Tool set - TOOL-KIT STANDARD - 1212422

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Toolbag case, equipped with: ferrule crimping pliers, stripping pliers, insulation stripper, cable cutter, screwdriver bladed: 0.6x3.5, 50 pcs. 5-pos. junction box connectors up to 2.5 mm<sup>2</sup>, tool compartment

### Product Features

- Rugged and heavy-duty tool bags
- Universal tool sets, with cutting, stripping, crimping, and testing tools from the TOOL fox tool range

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	1900.0 g
Custom tariff number	82060000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	165 mm
Width (a)	65 mm
Height	315 mm

#### General

Color	black
-------	-------

### Articles in set

Crimping pliers - CRIMPFOX 6S-F - 1212043



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.5 mm<sup>2</sup> ... 6 mm<sup>2</sup>, front entry, square crimp

## Tool set - TOOL-KIT STANDARD - 1212422

### Articles in set

#### Stripping tool - WIREFOX 10 - 1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

---

#### Stripping tool - WIREFOX-D 40 - 1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

---

#### Cable-cutting tool - CUTFOX 18 - 1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm<sup>2</sup>)

---

#### Screwdriver - SZF 1-0,6X3,5 - 1204517



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

---

#### Socket terminal block - JBC 2,5/5 - 3240165



5-pos. socket terminal block with spring-cage connection, for toolless wiring with push-in connection method, for one and multi-strand conductors with a cross section of 0.5 to 2.5 mm<sup>2</sup>, insulation housing transparent.

---

## Tool set - TOOL-KIT STANDARD - 1212422

### Articles in set

Tool bag, unequipped - TOOL-KIT STANDARD EMPTY - 1212423



Tool box, unequipped

---

### Classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21043090
eCl@ss 5.1	21043090
eCl@ss 6.0	21049190
eCl@ss 7.0	21049190
eCl@ss 8.0	21045003
eCl@ss 9.0	21045003

#### ETIM

ETIM 2.0	EC000149
ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### Approvals

#### Approvals

---

Approvals

EAC

## Tool set - TOOL-KIT STANDARD - 1212422

### Approvals

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

---