

Pointed pliers - MICROFOX-P ESD - 1212482

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



ESD electronic needle-nose pliers, smooth grip, with opening spring, non-reflective coating and phosphate-treated, 2-component grip

Product Features

- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- Opening spring for uniform, smooth opening
- Screwed precision-joint for permanent stability and optimum results
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working
- Made from special high-grade tool steel
- The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	79.9 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	125 mm
------------	--------

Classifications

eCl@ss

eCl@ss 4.0	21040301
------------	----------

Pointed pliers - MICROFOX-P ESD - 1212482

Classifications

eCl@ss

eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043706
eCl@ss 7.0	21043706
eCl@ss 8.0	21043817

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000833
ETIM 5.0	EC000833

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
