

Diagonal cutter - MICROFOX-SB - 1212489

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

Product Features

- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- Opening spring for uniform, smooth opening
- Through-connected joint for permanent stability and optimum distribution of force
- Made from special high-grade tool steel
- Mirror-polished and oiled metal surfaces, which provide maximum rust protection
- For a variety of applications

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	80.0 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	115 mm
------------	--------

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043706
eCl@ss 7.0	21043706

Diagonal cutter - MICROFOX-SB - 1212489

Classifications

eCl@ss

eCl@ss 8.0	21043711
------------	----------

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000165
ETIM 5.0	EC000165

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
