

Cable-cutting tool - CUTFOX-LB VDE - 1212527

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable cutter, for laminated busbars/ribbed tape, also for copper and aluminum up to 70 mm², VDE 1000 V AC/1500 V DC tested

Product Features

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	320.0 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	210 mm
------------	--------

General

Color	black
Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Classifications

eCl@ss

eCl@ss 4.0	21040302
eCl@ss 4.1	21040302

Cable-cutting tool - CUTFOX-LB VDE - 1212527

Classifications

eCl@ss

eCl@ss 5.0	21040302
eCl@ss 5.1	21040302
eCl@ss 6.0	21049011
eCl@ss 7.0	21049011
eCl@ss 8.0	21044701
eCl@ss 9.0	21044701

ETIM

ETIM 4.0	EC000142
ETIM 5.0	EC000142

UNSPSC

UNSPSC 6.01	23171604
UNSPSC 7.0901	23171604
UNSPSC 11	23171604
UNSPSC 12.01	23171604
UNSPSC 13.2	23171604

Approvals

Approvals


Approvals

VDE Zeichengenehmigung / EAC

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung 
--

EAC
