

Philips screwdriver - SF-PH 2-100 - 1212560

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, PH crosshead (lasered), uninsulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Product Features

- VDE approval
- Screwdrivers for Phillips screws with Pozidriv and Phillips Recess screw head



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	100.0 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade height	100 mm

General

Type	Phillips
	Straight
Material	Alloyed tool steel
Test standard	DIN ISO 8764-1

Standards and Regulations

Test standard	DIN ISO 8764-1
---------------	----------------

Philips screwdriver - SF-PH 2-100 - 1212560

Classifications

eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040406

ETIM

ETIM 4.0	EC000144
ETIM 5.0	EC000144

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Drawings

Pictogram

