

Crimping tool, pneumatic - ZAP 40 - 1212630


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Pneumatic crimping pliers, for ferrules according to DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross section 0.25 - 4 mm², trapezoid crimping, lateral entry



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 661027
GTIN	4046356661027
Weight per Piece (excluding packing)	720.000 g
Custom tariff number	84671900
Country of origin	Germany

Technical data

Dimensions

Length (b)	200 mm
Width (a)	44 mm
Height (c)	44 mm
Stripping length	0 mm

General

Compression	trapezoidal
Min. AWG, flexible, multi-strand	24
AWG max., flexible, multi-strand	12
Pressure range	4 bar ... 6 bar

Crimping tool, pneumatic - ZAP 40 - 1212630

Technical data

General

Air consumption per compression	0.2 l
Power consumption	0 W
Weight	0.4 kg
Min. cross section	0.25 mm ²
Max. cross section	4 mm ²

Classifications

eCl@ss

eCl@ss 10.0.1	17130101
eCl@ss 4.0	21040300
eCl@ss 4.1	21040300
eCl@ss 5.0	21040300
eCl@ss 5.1	17130100
eCl@ss 6.0	17130100
eCl@ss 7.0	17130101
eCl@ss 8.0	17130101
eCl@ss 9.0	17130101

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168
ETIM 6.0	EC002778
ETIM 7.0	EC002778

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Crimping tool, pneumatic - ZAP 40 - 1212630

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01744
-----	---	--------------------------

Accessories

Accessories

Cable end sleeve

Ferrule - AI 0,25- 6 YE - 3203024



Ferrule, sleeve length: 6 mm, length: 10.5 mm, color: yellow

Ferrule - AI 0,25- 8 YE - 3203037



Ferrule, sleeve length: 8 mm, length: 12.5 mm, color: yellow

Crimping tool, pneumatic - ZAP 40 - 1212630

Accessories

Ferrule - AI 0,5 - 8 WH - 3200014



Ferrule, sleeve length: 8 mm, length: 14 mm, color: white

Ferrule - AI 0,5 -10 WH - 3201275



Ferrule, sleeve length: 10 mm, length: 16 mm, color: white

Ferrule - AI 0,75- 8 GY - 3200519



Ferrule, sleeve length: 8 mm, length: 14 mm, color: gray

Ferrule - AI 0,75-10 GY - 3201288



Ferrule, sleeve length: 10 mm, length: 16 mm, color: gray

Ferrule - AI 1 - 8 RD - 3200030



Ferrule, sleeve length: 8 mm, length: 14 mm, color: red

Crimping tool, pneumatic - ZAP 40 - 1212630

Accessories

Ferrule - AI 1 -10 RD - 3200182



Ferrule, sleeve length: 10 mm, length: 16 mm, color: red

Ferrule - AI 1,5 - 8 BK - 3200043



Ferrule, sleeve length: 8 mm, length: 14 mm, color: black

Ferrule - AI 1,5 -10 BK - 3200195



Ferrule, sleeve length: 10 mm, length: 16 mm, color: black

Ferrule - AI 2,5 -10 BU - 3202533



Ferrule, sleeve length: 10 mm, length: 17 mm, color: blue

Ferrule - AI 2,5 -12 BU - 3200962



Ferrule, sleeve length: 12 mm, length: 18 mm, color: blue

Crimping tool, pneumatic - ZAP 40 - 1212630

Accessories

Ferrule - AI 4 -10 GY - 3200535



Ferrule, sleeve length: 10 mm, length: 17 mm, color: gray

Ferrule - AI 4 -12 GY - 3200959



Ferrule, sleeve length: 12 mm, length: 20 mm, color: gray
