

Diagonal cutter - CUTFOX-SP BOLT VDE - 1212831

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Power diagonal cutter, 200 mm, induction-hardened cutting, VDE 1000 V AC/ 1500 V DC tested

Why buy this product

- Inductively hardened blades for long-term stable cutting performance
- VDE-tested cutting tools made from special high-grade tool steel

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 045504
GTIN	4055626045504
Weight per Piece (excluding packing)	300.000 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	200 mm
Cable diameter	0.2 mm ... 4 mm

General

Test standard	DIN EN 60900 (VDE 0682 PART 201)
	DIN ISO 5746

Standards and Regulations

Test standard	DIN EN 60900 (VDE 0682 PART 201)
---------------	----------------------------------

Diagonal cutter - CUTFOX-SP BOLT VDE - 1212831

Technical data

Standards and Regulations

	DIN ISO 5746
--	--------------

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung  http://www.vde.com/en/Institute/OnlineService/VDE-approved-products/Pages/Online-Search.aspx 109845
