

Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² to 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion, equipped with fall protection

Why buy this product

- With a particularly small handle width, the tool fits perfectly in your hand
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping
- Pressure lock ensures consistently high quality crimping results



Key Commercial Data

Packing unit	1 STK
GTIN	4 055626 212678
GTIN	4055626212678
Weight per Piece (excluding packing)	460.000 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	180 mm
Width (a)	70 mm

General



Crimping pliers - CRIMPFOX CENTRUS 6S - 1213144

Technical data

General

Color	black	
Compression	Square crimp	
Type of contact	Insulated and uninsulated ferrules	
Designation	Crimping position 1	
Min. cross section	0.14 mm²	
Max. cross section	6 mm ²	
AWG min	26	
AWG max	10	

Approvals		
Approvals		
Approvals		
EAC		
Ex Approvals		
Approval details		
EAC EAC-Zulassung		

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com