

Protective covers - HC-B06-HCLWS-PLR-BK - 1414634

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective cover B6, with single locking latch, protective cover material: PA, height: 21.6 mm, seal: yes, diameter of retaining cord eyelet: 30 mm



COMPLETE

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 131184
GTIN	4055626131184
Weight per Piece (excluding packing)	46.000 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Length	60 mm
Width	43 mm
Height	21.6 mm
Diameter of retaining cord eyelet	30 mm

Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

General

Size	B6
------	----

Protective covers - HC-B06-HCLWS-PLR-BK - 1414634

Technical data

General

Type	for sleeve housing for single locking latch
Material	PA
Seal material	NBR
Flammability rating according to UL 94	HB
Color	black
Seal present	yes
Connection	Plastic protective cover for short-term protection

Standards and Regulations


Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 10.0.1	27440208
eCl@ss 4.0	23110100
eCl@ss 4.1	23110100

Protective covers - HC-B06-HCLWS-PLR-BK - 1414634

Classifications

eCl@ss

eCl@ss 5.0	23110100
eCl@ss 5.1	23110100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	--	--------------------------