

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Step-down adapter, M20 to M16, including O-ring



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 941512
Weight per Piece (excluding packing)	10.24 g
Custom tariff number	74153300
Country of origin	Germany

### Technical data

#### Dimensions

Length	9 mm
Length without connecting thread	2.5 mm
Connecting thread diameter	20 mm
Hexagon angular dimension GRP	24 mm
Length of the connecting thread	6.5 mm

#### Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

#### General

Material	Nickel-plated brass
Cable gland material	Nickel-plated brass

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611

### Technical data

#### General

O-ring material	NBR
Outer thread	M20
Internal thread	M16
Color	silver

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27439207

#### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938

#### UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

### Drawings

## Reducing adapter - REDUC-M-KV-M20/M16 - 1647611

Dimensional drawing

