

## Reducing adapter - REDUC-M-KV-M32/M25 - 1647637


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Reducing adapter, metal, M32 to M25, including O-ring



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 941536
Weight per Piece (excluding packing)	35.29 g
Custom tariff number	74153300
Country of origin	Germany

### Technical data

#### Dimensions

Length	11.5 mm
Length without connecting thread	3.5 mm
Connecting thread diameter	32 mm
Hexagon angular dimension GRP	37 mm
Length of the connecting thread	8 mm

#### Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

#### General

Material	Nickel-plated brass
Cable gland material	Nickel-plated brass

## Reducing adapter - REDUC-M-KV-M32/M25 - 1647637

### Technical data

#### General

O-ring material	NBR
Outer thread	M32
Internal thread	M25
Color	silver

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27439207

#### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938

#### UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

### Drawings

## Reducing adapter - REDUC-M-KV-M32/M25 - 1647637

Dimensional drawing

