

Housing - HC-D 50-AMQ - 1775868


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON panel mounting base B50, with double locking latch, height 28 mm



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 038410
Weight per Piece (excluding packing)	174.68 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	28 mm
Width	57 mm
Length	102 mm
Length of the assembly cutout	76 mm
Width of the assembly cutout	48 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D25, A16/A32
Type	D50
Housing type	Panel mounting base

Housing - HC-D 50-AMQ - 1775868

Technical data

General

Locking type	With double locking latch
Screw connection	none
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	Steel, galvanized

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / GL

Housing - HC-D 50-AMQ - 1775868

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC

GL

Drawings

Dimensional drawing

Dimensional drawing

Panel cutout

