

## Cable housing - KGS-MSTB 2,5/ 8 - 1783779

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 8, Dimension a: 40 mm, Color: green

### Product Features

- ✓ Straight cable outlet for sequencing several cable housings
- ✓ Easier plug-in and disconnection processes
- ✓ Suitable for cables with a diameter of 4 to 13.5 mm
- ✓ For MSTB, IC, and GMSTB plugs with and without flange, and pitch of 5.0 and 5.08 mm
- ✓ Full latching of both half shells of the cable housing
- ✓ Strain relief for the cables provided by cable binder or a clamp



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 041960
Weight per Piece (excluding packing)	15.15 g
Custom tariff number	85472000
Country of origin	Poland

### Technical data

#### Dimensions

Pitch	0.00 mm
Dimension a	40 mm

#### General

Range of articles	KGS-MSTB 2,5
Insulating material group	I

## Cable housing - KGS-MSTB 2,5/ 8 - 1783779

### Technical data

#### General

Insulating material	ABS
Flammability rating according to UL 94	HB
Number of positions	8

#### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

#### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000437
ETIM 5.0	EC000437

#### UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

### Approvals

#### Approvals

---

Approvals

EAC

---

## Cable housing - KGS-MSTB 2,5/ 8 - 1783779

### Approvals

Ex Approvals

---

Approvals submitted

---

Approval details

EAC
-----

### Drawings

Dimensional drawing

