

Cable housing - KGS-MSTB 2,5/12 - 1783818

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 12, Dimension a: 60 mm, Color: green

Product Features

- ✓ Straight cable outlet for sequencing several cable housings
- ✓ Easier plug-in and disconnection processes
- ✓ Suitable for cables with a diameter of 4 to 13.5 mm
- ✓ Full latching of both half shells of the cable housing
- ✓ For MSTB, IC, and GMSTB plugs with and without flange, and pitch of 5.0 and 5.08 mm
- ✓ Strain relief for the cables provided by cable binder or a clamp



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 041991
Weight per Piece (excluding packing)	19.8 g
Custom tariff number	85472000
Country of origin	Poland

Technical data

Dimensions

Pitch	0 mm
Dimension a	60 mm

General

Range of articles	KGS-MSTB 2,5
Insulating material group	I

Cable housing - KGS-MSTB 2,5/12 - 1783818

Technical data

General

Insulating material	ABS
Inflammability class according to UL 94	HB
Number of positions	12

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27449202
eCl@ss 8.0	27440202

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

EAC

Ex Approvals

Cable housing - KGS-MSTB 2,5/12 - 1783818

Approvals

Approvals submitted

Approval details

EAC

Drawings

Dimensional drawing

