

## Cable housing - KGG-MC 1,5/ 8 - 1834408

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 3.81 mm, Number of positions: 8, Dimension a: 32.87 mm, Color: green

### Product Features

- For MC or IMC plugs with and without flange, and 3.81 mm pitch
- Straight cable outlet for sequencing several cable housings
- Easier plug-in and disconnection processes
- Incl. cable binders and marker strips for any numbers of positions
- Incl. transparent label carriers from 6- to 16-pos.
- Full latching of both half shells of the cable housing
- Strain relief for the cables provided by cable binder or a clamp



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| Minimum order quantity               | 10 pc   |
| GTIN                                 | <br>4 017918 051921 |
| Weight per Piece (excluding packing) | 8.61 g  |
| Custom tariff number                 | 85389099  |
| Country of origin                    | Poland  |

### Technical data

#### Dimensions

|             |          |
|-------------|----------|
| Pitch       | 3.81 mm  |
| Dimension a | 32.87 mm |

#### General

## Cable housing - KGG-MC 1,5/ 8 - 1834408

### Technical data

#### General

|  |            |
|--|------------|
| Range of articles                      | KGG-MC 1,5 |
| Insulating material group              | I          |
| Insulating material                    | ABS        |
| Flammability rating according to UL 94 | HB         |
| Number of positions                    | 8          |

#### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | HB |
|--|----|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440202 |
| eCl@ss 9.0 | 27440202 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC000879 |
| ETIM 5.0 | EC000437 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

### Approvals

#### Approvals

---

## Cable housing - KGG-MC 1,5/ 8 - 1834408

### Approvals

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

### Drawings

Dimensional drawing

