

Cable housing - KGS-PC 4/ 6-F - 1837353

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable housing, Pitch: 0 mm, Number of positions: 6, Dimension a: 47.52 mm, Color: green

Product Features

- ✓ Ergonomic cable housing for standard PC 4 plugs with screw connection
- ✓ A cable clamp can be mounted back to front
- ✓ KGG-PC 4 for cable diameters from 4 to 13.5 mm²
- ✓ KGS-PC 4 (angled cable outlet) for cable diameters from 6 to 16 mm²



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 111366
Weight per Piece (excluding packing)	27.0 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Pitch	0.00 mm
Dimension a	47.52 mm

General

Range of articles	KGS-PC 4/...-F
Insulating material group	0
Insulating material	ABS
Flammability rating according to UL 94	HB

Cable housing - KGS-PC 4/ 6-F - 1837353

Technical data

General

Number of positions	6
---------------------	---

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

EAC

Ex Approvals

Cable housing - KGS-PC 4/ 6-F - 1837353

Approvals

Approvals submitted

Approval details

EAC

Drawings

Dimensional drawing

