

Components of electronic housing - UM-PRO 72 COVER-L BK - 2200151

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Seitenelement (links) mit Montagefuß für die Tragschiene für UM-PRO-Profile der Leiterplattenbreite 72 mm



The figure shows the 122 mm wide version

Product Features

- Item is from the UM-BASIC/UM-PRO product range
- PVC press-drawn section (UM-BASIC) or PA (UM-PRO)
- Available in individual lengths
- Available in the overall widths of 72 mm, 108 mm, and 122 mm
- Variety of connection technologies
- Can be mounted on the DIN rail



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	14.0 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

General

Housing type	Panel mounting base
Housing material	Polyamide
Color	black

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

Dimensions

Components of electronic housing - UM-PRO 72 COVER-L BK - 2200151

Technical data

Dimensions

Length	15.5 mm
Constructional height	40 mm
Width	92.29 mm

Technical data

Inflammability class according to UL 94	V0
---	----

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27182003
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC000721

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized

Components of electronic housing - UM-PRO 72 COVER-L BK - 2200151

Approvals

Ex Approvals

Approvals submitted

Approval details

UL Recognized 

Drawings

Dimensional drawing

