

## Side element - UM-ALU 4-72 COVER PA BK - 2200934

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Press-drawn section housings, Side elements (left and right), incl. snap-on foot, width: 75.4 mm, color: black (9005)



### Your advantages

- Item is from the UM-ALU product range
- Aluminum press-drawn section
- Available in lengths from 42.5 mm ... 990 mm, can be cut to any length
- Available in overall widths of 75 mm and 105 mm
- Variety of connection technologies
- Can be mounted on the DIN rail
- EMC protection

### Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356716529
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	39269097
Country of origin	Hungary

### Technical data

#### Product properties

Brief article description	Side element
Type	UM-ALU 4-72 COVER PA BK
Order No.	2200934

## Side element - UM-ALU 4-72 COVER PA BK - 2200934

### Technical data

#### Product properties

Housing type	Press-drawn section housings
Type	Side elements (left and right), incl. snap-on foot
Mounting type	Screw mounting

#### Dimensions

Width [ w ]	75.4 mm
-------------	---------

#### Material specifications

Housing material	PA
Color (RAL)	black (9005)
Flammability rating according to UL 94	V0

#### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

#### Packaging specifications

Type of packaging	packed in cardboard
Pieces per package	1
Denomination packing units	Pcs.
Outer packaging type	Carton

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27182701
eCl@ss 4.0	27180400
eCl@ss 4.1	27180400
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27182000
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701
eCl@ss 9.0	27182701

## Side element - UM-ALU 4-72 COVER PA BK - 2200934

### Classifications

#### ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC000721
ETIM 5.0	EC002779
ETIM 6.0	EC002779
ETIM 7.0	EC002779

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

### Approvals

#### Approvals

---

#### Approvals


#### EAC

---

#### Ex Approvals

---

#### Approval details

EAC		B.01742
-----	---	---------

### Accessories

#### Accessories

Component housing lower part

## Side element - UM-ALU 4-72 COVER PA BK - 2200934

### Accessories

Profile - UM-ALU 4-72 PROFILE 42,5 - 2200917



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 42.5 mm

---

Profile - UM-ALU 4-72 PROFILE 60 - 2200918



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 60 mm

---

Profile - UM-ALU 4-72 PROFILE 95 - 2200919



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 95 mm

---

Profile - UM-ALU 4-72 PROFILE 130 - 2200920



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 130 mm

---

Profile - UM-ALU 4-72 PROFILE 165 - 2200921



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 165 mm

---

## Side element - UM-ALU 4-72 COVER PA BK - 2200934

### Accessories

Profile - UM-ALU 4-72 PROFILE 200 - 2200922



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 200 mm

---

Profile - UM-ALU 4-72 PROFILE 235 - 2200923



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 235 mm

---

Profile - UM-ALU 4-72 PROFILE 990 - 2200924



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 990 mm

---

Profile - UM-ALU 4-72 PROFILE 111 - 2201930



Press-drawn section housings, Basic profile, Profile width (internal): 72 mm, length: 111 mm

---