

Media module - FL SFP WDM10-A - 2702440

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Gigabit SFP WDM module for transmission up to a maximum of 10 km on a single fiber with a wavelength of 1310/1550 nm.

Product Description

SFP WDM module with a data transmission speed of 1000 Mbps, a wavelength of 1310/1550 nm, and a maximum transmission length of 10 km.

Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 193854
GTIN	4055626193854
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)

Interfaces

Interface	Ethernet FO
-----------	-------------

Media module - FL SFP WDM10-A - 2702440

Technical data

Interfaces

No. of ports	1 (LC single mode)
Transmission physics	Single-mode fiberglass
Transmission speed	1 Gbps
Transmission length	10 km (Fiberglass 9/125)
Wavelength	1310 nm (TX)
	1550 nm (RX)
Signal LEDs	depending on the Factoryline device

Function

Basic functions	SFP module as FO port
Status and diagnostic indicators	via a Factoryline device

Supply voltage

Supply voltage	3.3 V (via Factoryline switch)
Max. current consumption	300 mA
Current consumption	300 mA

General

Mounting type	Insert in SFP slot
Type AX	Factoryline devices with SFP slot
Net weight	32.1 g
Housing material	Metal
MTTF	124 Years (Telcordia SR-332, temperature factor at 40°C = 1, stress factor at 50% = 1, environmental factor = 1)

Classifications

eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	27149249
eCl@ss 9.0	19179290

Media module - FL SFP WDM10-A - 2702440

Classifications

ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC002609
ETIM 6.0	EC000310
ETIM 7.0	EC000310

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	26121650
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604

Approvals

Approvals

Approvals

DNV GL / LR / BSH / RINA / ABS / NK / BV

Ex Approvals




Approval details

DNV GL		https://approvalfinder.dnvgl.com/	TAA00000YV
--------	--	---	------------

LR		http://www.lr.org/en	17/20056
----	--	---	----------

Media module - FL SFP WDM10-A - 2702440

Approvals

BSH			Nr. 966
RINA		http://www.rina.org/en	ELE130419XG
ABS		http://www.eagle.org/eagleExternalPortalWEB/	17- HG1592765-1-PDA
NK		http://www.classnk.or.jp/hp/en/	TA19464M
BV		http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials	48146/A1 BV