

Insertion bridge - EB 80- DIK BU - 2715940


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insertion bridge, pitch: 6.2 mm, number of positions: 80, color: blue

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 061692
GTIN	4017918061692
Weight per Piece (excluding packing)	34.800 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Technical data

Color	blue
Material	CU
Number of positions	80
Pitch	6.2 mm

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Insertion bridge - EB 80- DIK BU - 2715940

Classifications

eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140
eCl@ss 9.0	27141140

ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000489
ETIM 6.0	EC000489
ETIM 7.0	EC000489

UNSPSC

UNSPSC 6.01	30211829
UNSPSC 7.0901	39121426
UNSPSC 11	39121426
UNSPSC 12.01	39121426
UNSPSC 13.2	39121426

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approval details

Insertion bridge - EB 80- DIK BU - 2715940

Approvals

EAC		EAC-Zulassung
-----	---	---------------

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------