

Wiring bridge - MPB 18/1- 8 - 2748577

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 8-pos.

Your advantages

- In combination with other devices in the distribution board, such as residual current devices and miniature circuit breakers
- Practical wiring of all common applications
- For combinations of lightning and surge arresters
- End covers are used to terminate and insulate individually cut bridges

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 062545
GTIN	4017918062545
Weight per Piece (excluding packing)	39.500 g
Custom tariff number	85369095
Country of origin	Germany

Technical data

Dimensions

Height	144.4 mm
--------	----------

General

Nominal current I_N	100 A
Number of positions	8

Wiring bridge - MPB 18/1- 8 - 2748577

Technical data

General

Color	gray
Housing material	Plastic
Type	Comb bridge

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27140299
eCl@ss 4.1	27140299
eCl@ss 5.0	27140202
eCl@ss 5.1	27140200
eCl@ss 6.0	27371300
eCl@ss 7.0	27371306
eCl@ss 8.0	27371306
eCl@ss 9.0	27371306

ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000215
ETIM 6.0	EC000215
ETIM 7.0	EC000215

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals

Wiring bridge - MPB 18/1- 8 - 2748577

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------
