

Zack marker strip - ZBN 18:UNBEDRUCKT - 2809128

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Zack marker strip, Strip, white, Unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 18 mm, Lettering field: 18 x 5 mm

Product Features

- Can be labeled with CMS computer marking system or by hand using B-STIFT
- Consists of five individual labels with 17.5 mm pitch
- Flat zack marker strips

Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 076245
Weight per Piece (excluding packing)	0.82 GRM
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	17.5 mm
-----------	---------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	5

Zack marker strip - ZBN 18:UNBEDRUCKT - 2809128

Technical data

General

Number of individual labels per row	5
Number of marker strips	5

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410