

## Wiring bridge - MPB 18/1-57 - 2809238

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 57-pos.

### Your advantages

- In combination with other devices in the distribution board, such as residual current devices and miniature circuit breakers
- Practical wiring of all common applications
- End covers are used to terminate and insulate individually cut bridges
- For combinations of lightning and surge arresters

### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 pc  |
| GTIN                                 | <br>4 017918 076306 |
| GTIN                                 | 4017918076306   |
| Weight per Piece (excluding packing) | 307.500 g   |
| Custom tariff number                 | 85369095  |
| Country of origin                    | Germany   |

### Technical data

#### General

|                       |             |
|-----------------------|-------------|
| Nominal current $I_N$ | 100 A       |
| Number of positions   | 57          |
| Color                 | gray        |
| Housing material      | Plastic     |
| Type                  | Comb bridge |

## Wiring bridge - MPB 18/1-57 - 2809238

### Technical data

#### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140200 |
| eCl@ss 4.1 | 27140200 |
| eCl@ss 5.0 | 27140200 |
| eCl@ss 5.1 | 27140200 |
| eCl@ss 6.0 | 27371300 |
| eCl@ss 7.0 | 27371306 |
| eCl@ss 8.0 | 27371306 |
| eCl@ss 9.0 | 27371306 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000489 |
| ETIM 3.0 | EC000489 |
| ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000215 |
| ETIM 6.0 | EC000215 |
| ETIM 7.0 | EC000215 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30212010 |
| UNSPSC 7.0901 | 39121610 |
| UNSPSC 11     | 39121610 |
| UNSPSC 12.01  | 39121610 |
| UNSPSC 13.2   | 39121620 |

### Approvals

#### Approvals

---

Approvals

EAC

---

## Wiring bridge - MPB 18/1-57 - 2809238

### Approvals

Ex Approvals

---

#### Approval details

|     |   |                          |
|-----|---|--------------------------|
| EAC |  | RU C-<br>DE.A*30.B.01742 |
|-----|---|--------------------------|

---