

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Patch cable, CAT5, assembled, 0.5 m



Ethernet

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	35.66 g
Custom tariff number	85444210
Country of origin	Poland

Technical data

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

External sheath

Outer sheath, material	LSFROH
External diameter	5.5 mm
External diameter max.	6.2 mm

Single wire

Individual wires per module	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm ²

Mechanical properties

Smallest bending radius, fixed installation	30 mm
---	-------

General

Conductor length	0.5 m
Nominal voltage U _N	150 V _{rms}

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Technical data

Behavior in fire

Flame resistance	According to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-1

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-1
Flame resistance	According to IEC 60332-3C
Standards/regulations	CAT5

Classifications

eCl@ss

eCl@ss 4.0	27250591
eCl@ss 4.1	27240409
eCl@ss 5.0	27259207
eCl@ss 5.1	27061801
eCl@ss 6.0	27259207
eCl@ss 7.0	27259207
eCl@ss 8.0	27060308

ETIM

ETIM 2.0	EC001262
ETIM 3.0	EC001262
ETIM 4.0	EC001262
ETIM 5.0	EC001262

UNSPSC

UNSPSC 6.01	26121609
UNSPSC 7.0901	26121609
UNSPSC 11	26121609
UNSPSC 12.01	26121609
UNSPSC 13.2	26121609

Approvals

Approvals

Patch cable - FL CAT5 PATCH 0,5 - 2832263

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
