

## Media module - FL SFP FX - 2891081

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The small form-factor plug-in module provides a fiber optic interface with a data transmission speed of 100 Mbps with a wavelength of 1310 nm (long).


### Your advantages

- Network structure according to IEC 61850
- IEEE 1613

RoHS

IEC 61850-3

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 800952
GTIN	4046356800952
Weight per Piece (excluding packing)	20.000 g
Custom tariff number	85176200
Country of origin	Taiwan

### Technical data

#### Dimensions

Width	13.7 mm
Height	8.95 mm
Length	56.5 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C (non-condensing)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (non-condensing)
Permissible humidity (operation)	30 % ... 95 % (non-condensing)

# Media module - FL SFP FX - 2891081

## Technical data

### Ambient conditions

Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (1500 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

### Interfaces

Interface	Ethernet FO
No. of ports	1 (LC multi-mode)
Transmission physics	multi-mode fiberglass
Transmission speed	100 Mbps
Transmission length	typ. 2 km
Wavelength	1310 nm
Signal LEDs	depending on the Factoryline device

### Function

Basic functions	SFP module as FO port
Status and diagnostic indicators	via a Factoryline device

### Supply voltage

Supply voltage	3.3 V (via Factoryline switch)
----------------	--------------------------------

### General

Mounting type	Insert in SFP slot
Type AX	Factoryline devices with SFP slot
Net weight	30.1 g
Housing material	Metal

### Standards and Regulations

Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500

# Media module - FL SFP FX - 2891081

## Classifications

### eCl@ss

eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170106
eCl@ss 8.0	27149249
eCl@ss 9.0	19179290

### ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC002609
ETIM 6.0	EC000310
ETIM 7.0	EC000310

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	26121650
UNSPSC 18.0	43222604
UNSPSC 19.0	43222604
UNSPSC 20.0	43222604
UNSPSC 21.0	43222604

## Approvals

### Approvals

---

#### Approvals

DNV GL / LR / BSH / RINA / ABS / NK / BV / EAC

---

#### Ex Approvals

---

### Approval details

# Media module - FL SFP FX - 2891081

## Approvals

DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAA00000YV
LR		<a href="http://www.lr.org/en">http://www.lr.org/en</a>	17/20056
BSH			Nr. 966
RINA		<a href="http://www.rina.org/en">http://www.rina.org/en</a>	ELE130419XG
ABS		<a href="http://www.eagle.org/eagleExternalPortalWEB/">http://www.eagle.org/eagleExternalPortalWEB/</a>	17- HG1592765-1-PDA
NK		<a href="http://www.classnk.or.jp/hp/en/">http://www.classnk.or.jp/hp/en/</a>	TA19464M
BV		<a href="http://www.veristar.com/portal/veristarinfo/generalinfo/approved/approvedProducts/equipmentAndMaterials">http://www.veristar.com/portal/veristarinfo/generalinfo/ approved/approvedProducts/equipmentAndMaterials</a>	48146/A1 BV
EAC			RU *- DE.A*08.B.00731

## Accessories

### Accessories

Data cable preassembled

FO patch cable - FOC-LC:PA-SC:PA-OM2:D01/1 - 1115607



## Media module - FL SFP FX - 2891081

### Accessories

---

FO patch cable - FOC-LC:PA-SC:PA-OM2:D01/2 - 1115605



FO patch cable - FOC-SC:PA-SC:PA-OM2:D01/1 - 1115536



Multi-mode OM2 duplex jumper, SC-SC, UPC polishing, length 1 m

FO patch cable - FOC-SC:PA-SC:PA-OM2:D01/2 - 1115535



Multi-mode OM2 duplex jumper, SC-SC, UPC polishing, length 2 m

FO patch cable - FOC-ST:PA-SC:PA-OM2:D01/1 - 1115574



Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 1 m

FO patch cable - FOC-ST:PA-SC:PA-OM2:D01/2 - 1115573



Multi-mode OM2 duplex jumper, ST-SC, UPC polishing, length 2 m

## Media module - FL SFP FX - 2891081

### Accessories

FO patch cable - FOC-LC:PA-SC:PA-OM4:D01/1 - 1115601



Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 1 m

---

FO patch cable - FOC-LC:PA-SC:PA-OM4:D01/2 - 1115600



Multi-mode OM4 duplex jumper, LC-SC, UPC polishing, length 2 m

---

FO patch cable - FOC-SC:PA-SC:PA-OM4:D01/1 - 1115424



Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 1 m

---

FO patch cable - FOC-SC:PA-SC:PA-OM4:D01/2 - 1115423



Multi-mode OM4 duplex jumper, SC-SC, UPC polishing, length 2 m

---