

## Patch cable - FL CAT6 PATCH 5,0 - 2891783

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Patch cable, CAT6, pre-assembled, 5.0 m



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 167574
GTIN	4046356167574
Weight per Piece (excluding packing)	200.000 g
Custom tariff number	85444210
Country of origin	Poland

### Technical data

#### Cable type

Fixed cable length	5.00 m
Shielding	S/FTP

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
---------------------------------	------------------

#### External sheath

Outer sheath, material	LSFROH
External diameter	5.50 mm
External diameter max.	6.2 mm

#### Single wire

## Patch cable - FL CAT6 PATCH 5,0 - 2891783

### Technical data

#### Single wire

Single wires, quantity	8
Single wire, material	Cu litz wire
Single wire, cross section	0.14 mm <sup>2</sup>

#### Mechanical properties

Smallest bending radius, fixed installation	30 mm
---	-------

#### General

Conductor length	5.00 m
Nominal voltage U <sub>N</sub>	150 V <sub>rms</sub>
Transmission characteristics (category)	CAT6
Transmission speed	1 Gbps
Degree of protection	IP20
Contact resistance	≤ 0.003 Ω (IEC 60603-7)

#### Behavior in fire

Flame resistance	according to IEC 60332-3C
Concentration of fumes	in accordance with IEC 61034
Halogen-free	according to IEC 60754-1

#### Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	according to IEC 60332-3C
Halogen-free	according to IEC 60754-1
Flammability rating according to UL 94	V0

#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Classifications

#### eCl@ss

eCl@ss 10.0.1	27060308
eCl@ss 11.0	27060308
eCl@ss 4.0	27250500
eCl@ss 4.1	27250500
eCl@ss 5.0	27259200
eCl@ss 5.1	27259200
eCl@ss 6.0	27259200

# Patch cable - FL CAT6 PATCH 5,0 - 2891783

## Classifications

### eCl@ss

eCl@ss 7.0	27060308
eCl@ss 9.0	27060308

### ETIM

ETIM 2.0	EC001262
ETIM 3.0	EC001262
ETIM 4.0	EC001262
ETIM 6.0	EC001262
ETIM 7.0	EC001262

### UNSPSC

UNSPSC 6.01	26121609
UNSPSC 7.0901	26121609
UNSPSC 11	26121609
UNSPSC 12.01	26121609
UNSPSC 13.2	26121604
UNSPSC 18.0	26121604
UNSPSC 19.0	26121604
UNSPSC 20.0	26121604
UNSPSC 21.0	26121604

## Approvals

### Approvals

---

#### Approvals

EAC / EAC-RoHS

---

#### Ex Approvals

---

### Approval details

EAC		19060508
-----	---	----------

## Patch cable - FL CAT6 PATCH 5,0 - 2891783

### Approvals

EAC-RoHS



B.00385/20

### Accessories

#### Accessories

#### Color-coding

##### Color-coding - FL PATCH CCODE BK - 2891194



Color marking for patch cable, black

##### Color-coding - FL PATCH CCODE BN - 2891495



Color marking for patch cable, brown

##### Color-coding - FL PATCH CCODE BU - 2891291



Color marking for patch cable, blue

##### Color-coding - FL PATCH CCODE GN - 2891796



Color marking for patch cable, green

## Patch cable - FL CAT6 PATCH 5,0 - 2891783

### Accessories

Color-coding - FL PATCH CCODE GY - 2891699



Color marking for patch cable, gray

---

Color-coding - FL PATCH CCODE RD - 2891893



Color marking for patch cable, red

---

Color-coding - FL PATCH CCODE VT - 2891990



Color marking for patch cable, purple

---

Color-coding - FL PATCH CCODE YE - 2891592



Color marking for patch cable, yellow

---

### Safety locking

Port Guard Security Element - FL PATCH GUARD - 2891424



Lockable security element

---

## Patch cable - FL CAT6 PATCH 5,0 - 2891783

### Accessories

Port Guard Security Element - FL PATCH SAFE CLIP - 2891246



Security element for FL patch cable