

Plug-in module - RIF-LDP-48-60 DC - 2900940

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with freewheeling diode and yellow LED, polarity: A1+, A2-, input voltage: 48 - 60 V DC $\pm 20\%$

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	4.0 g
Custom tariff number	85363010
Country of origin	China

Technical data

Input data

Input voltage range	48 V DC ... 60 V DC $\pm 20\%$
Status display	Yellow LED
Protective circuit/component	Damping diode

Standards and Regulations

Connection in acc. with standard	CSA
----------------------------------	-----

Classifications

eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371010

Plug-in module - RIF-LDP-48-60 DC - 2900940

Classifications

ETIM

ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC000683

UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39121516

Approvals

Approvals

Approvals

UL Recognized / CSA / EAC / GL / LR / EAC

Ex Approvals

Approvals submitted

Approval details

UL Recognized

CSA

EAC

GL

Plug-in module - RIF-LDP-48-60 DC - 2900940

Approvals

LR

EAC
