

Front adapters - FLKM-PA-D37/HW/AID4/C300 - 2905321

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE front adapter, for Honeywell C300, series C I/O, max. 1 x 16 channels with configuration plug and 37-pos. D-SUB connector

Product Features

- Prewired connector with configuration plug
- Pre-assembled system cables are connected directly to I/O modules using the front adapters
- Front adapter with D-SUB connector
- Connection of analog modules



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	100.0 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	< 50 V AC
	60 V DC
Max. permissible current	1 A (per path)
Mounting position	any
Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103

Front adapters - FLKM-PA-D37/HW/AID4/C300 - 2905321

Technical data

General

Degree of pollution	2
Overvoltage category	II

Connection data 1

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

Supported controller

Controller	HONEYWELL Experion PKS C300/C-Series
- suitable I/O card	TAIX01 (non-redundant)
	TAIX11 (redundant)
	TAOX01 (non-redundant)
	TAOX11 (redundant)
	TAIXA1
	TAIXB1

Standards and Regulations

Standards/regulations	DIN EN 50178
	IEC 60664
	IEC 62103
Degree of pollution	2
Overvoltage category	II

Classifications

eCl@ss

eCl@ss 5.1	27250313
eCl@ss 6.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 4.0	EC001423
ETIM 5.0	EC001423

Approvals

Approvals

Front adapters - FLKM-PA-D37/HW/AID4/C300 - 2905321

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized	
mm ² /AWG/kcmil	30-12
Nominal current I _N	1 A
Nominal voltage U _N	125 V

cUL Recognized	
mm ² /AWG/kcmil	30-12
Nominal current I _N	1 A
Nominal voltage U _N	125 V


EAC

cULus Recognized 

Drawings

Front adapters - FLKM-PA-D37/HW/AID4/C300 - 2905321

Circuit diagram



Connection scheme: FLKM-PA-D37/HW/AN/C300

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>