

## Thermomagnetic device circuit breaker - TMC 7/8 AUX - 2908219

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermomagnetic device circuit breaker, Number of positions: 1, Connection method: Screw, Cross section: 1 mm<sup>2</sup>- 35 mm<sup>2</sup>, AWG: 18 - 2, Width: 9 mm, Mounting type: Snaps on to side of circuit breaker, Color: gray



### Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	150.000 g
Custom tariff number	85362010
Country of origin	China

### Technical data

#### General

Mounting type	Snaps on to side of circuit breaker
Color	gray
Number of positions	1

#### Electrical data

Operating voltage	120 V AC ... 277 V AC
	24 V DC ... 125 V DC
Rated current I <sub>N</sub>	6 A (12 ... 240 V AC)
	3 A (277 V AC)
	6 A (12 ... 24 V DC)
	2 A (48 V DC)
	1 A (130 V DC)

#### Dimensions

Height	85.8 mm
Width	9 mm

# Thermomagnetic device circuit breaker - TMC 7/8 AUX - 2908219

## Technical data

### Dimensions

Depth	65.7 mm
-------	---------

### Ambient conditions


Ambient temperature (operation)	-35 °C ... 70 °C
---------------------------------	------------------

### Connection data

Conductor cross section solid min.	1 mm <sup>2</sup>
Conductor cross section solid max.	35 mm <sup>2</sup>
Conductor cross section flexible min.	1 mm <sup>2</sup>
Conductor cross section flexible max.	35 mm <sup>2</sup>
Conductor cross section AWG min.	18
Conductor cross section AWG max.	2
Connection method	Screw
Tightening torque max	1 Nm

## Drawings

Dimensional drawing



## Classifications

### eCl@ss

eCl@ss 5.1	27379201
eCl@ss 8.0	27130806
eCl@ss 9.0	27130806

### ETIM

ETIM 5.0	EC000942
----------	----------

# Thermomagnetic device circuit breaker - TMC 7/8 AUX - 2908219

## Approvals

### Approvals

---

#### Approvals


UL Listed / cUL Listed / cULus Listed

---


#### Ex Approvals

---

### Approval details

UL Listed  <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 478429

cUL Listed  <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm> FILE E 478429

cULus Listed 

---