

## Electronic housing - UM100-PROFIL 100CM - 2914563

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Panel mounting base, Lower part, Color: green, Width: 1000 mm, Note: required profile length = PCB length - 3.6 mm



### Product Features

- Lateral elements with potential ground contact available from the PCB to the DIN rail (EMC)
- Inexpensive as a result of reducing the number of separate housing parts
- Flexible size and shape
- Fast assembly on standard NS 35 or NS 32 DIN rails
- Wide range of options for external conductor connection
- High degree of mechanical stability by screwing the lateral elements to the profile
- The modules can be marked with Phoenix Contact marking material using the marking grooves in the press-drawn section



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	400.0 g
Custom tariff number	39162000
Country of origin	Germany

### Technical data

#### General

Housing type	Panel mounting base
Housing material	PVC
Color	green

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

#### Dimensions

Length	1 m
--------	-----

# Electronic housing - UM100-PROFIL 100CM - 2914563

## Technical data

### Dimensions

Width	1000 mm
-------	---------

### Technical data

Flammability rating according to UL 94	V0
--	----

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182701
eCl@ss 8.0	27182701

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC002779


### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Drawings

## Electronic housing - UM100-PROFIL 100CM - 2914563

Dimensional drawing



Dimensional drawing

