

Memory - SD FLASH 512MB - 2988146

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Program and configuration memory, plug-in, 512 Mbyte.

Similar figure

Your advantages

- Easy device replacement
- Easy reproduction of configurations
- Program and configuration memory, plug-in
- For storing application programs and other files in the file system of the PLC

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 342674
GTIN	4046356342674
Weight per Piece (excluding packing)	10.000 g
Custom tariff number	85235110
Country of origin	Taiwan

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Supply voltage	3.3 V DC
Supply voltage range	2.7 V DC ... 3.6 V DC

Memory - SD FLASH 512MB - 2988146

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27240403
eCl@ss 4.1	27240403
eCl@ss 5.0	27242212
eCl@ss 5.1	24210100
eCl@ss 6.0	27242200
eCl@ss 7.0	27242212
eCl@ss 8.0	27242212
eCl@ss 9.0	27242212

ETIM

ETIM 3.0	EC000192
ETIM 4.0	EC000192
ETIM 5.0	EC000192
ETIM 6.0	EC000192
ETIM 7.0	EC000192

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	32101601
UNSPSC 13.2	43202005

Accessories

Accessories

Controller

Memory - SD FLASH 512MB - 2988146

Accessories

Controller - ILC 131 ETH - 2700973



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 131 ETH/XC - 2701034



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

Controller - ILC 151 ETH - 2700974



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 151 ETH/XC - 2701141



Inline controller for use under harsh ambient conditions, with Ethernet interface for coupling to other controllers and systems, with programming options according to IEC 61131-3, complete with connector and labeling field.

Controller - ILC 171 ETH 2TX - 2700975



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Memory - SD FLASH 512MB - 2988146

Accessories

Controller - ILC 191 ETH 2TX - 2700976



The Inline controller offers the option of communicating via PROFINET and Modbus/TCP. Programming is carried out using PC Worx Express or PC Worx (IEC 61131-3).

Controller - ILC 191 ME/AN - 2700074



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, analog inputs (0 ... 10 V), and analog outputs (0 ... 10 V), with programming options according to IEC 61131-3

Controller - ILC 191 ME/INC - 2700075



Inline controller with integrated pulse/direction/PWM interface, RS-485/RS-422, fast counters, and incremental encoder inputs, with programming options according to IEC 61131-3

Controller - AXC 1050 - 2700988



Axio control for direct open-loop control of Axioline I/Os. With 2 Ethernet interfaces and programming capabilities according to IEC 61131-3. Complete with connector connector and labeling field.

Controller - AXC 1050 XC - 2701295



Axiocontrol for the direct control of Axioline I/Os. With 2 Ethernet interfaces, extended temperature range, and programming options according to IEC 61131-3. Complete with connector connector and marking field.
