

## Plug-in bridge - FBSR 4-6 - 3001595


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug-in bridge, Pitch: 6.2 mm, Number of positions: 4, Color: red

The figure shows a similar product

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 046356 891172
GTIN	4046356891172
Weight per Piece (excluding packing)	100.000 g
Custom tariff number	85389099
Country of origin	China

### Technical data

#### Technical data

Color	red
Material	Copper
Number of positions	4
Pitch	6.2 mm
Flammability rating according to UL 94	V0
Maximum load current	24 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

# Plug-in bridge - FBSR 4-6 - 3001595

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141140
eCl@ss 5.1	27141140
eCl@ss 6.0	27141140
eCl@ss 7.0	27141140
eCl@ss 8.0	27141140
eCl@ss 9.0	27141140

### ETIM

ETIM 4.0	EC000489
ETIM 5.0	EC000489
ETIM 6.0	EC000489

### UNSPSC

UNSPSC 6.01	30211829
UNSPSC 7.0901	39121426
UNSPSC 11	39121426
UNSPSC 12.01	39121426
UNSPSC 13.2	39121426

## Accessories

### Accessories

#### Cutting tools

Front cutter - CUTFOX-FBS - 1212124



Cutting tool, for separating individual jumper bars from FBS ... plug-in bridges and EB ... insertion bridges

## Plug-in bridge - FBSR 4-6 - 3001595

### Accessories

#### Protective cap

Protective cap - FBSC - 3012325



Covering hood, provides reliable shock protection when using cut-to-length FBS ...-5 and FBS ...-6 bridges, color: red