

## Test adapter - PAI-4-FIX GY - 3032790

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



4 mm test adapter, for terminal blocks with 8.2 mm pitch

### Product Features

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	2.2 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### Dimensions

Height	51.50 mm
Diameter	5.80 mm

#### General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in Do not plug in while the power is connected
Color	gray

Material	Copper alloy
Ambient temperature (operation)	-40 °C ... 125 °C

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

# Test adapter - PAI-4-FIX GY - 3032790

## Classifications

### eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27440313

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002255

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Approvals

### Approvals

---

Approvals

EAC / EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

## Test adapter - PAI-4-FIX GY - 3032790

### Approvals

EAC
-----