

Cover profile carrier - APH-ME - 3034374

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover profile carrier, for mounting on NS 35/7,5 DIN rail, for fixing the AP-ME cover profile, can be sealed as an option

Product Features

- The APH-ME end bracket is used in conjunction with the AP-ME cover
- It offers parking options for FBS ...-8 plug-in bridges and can be sealed as an option



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	35.0 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	138 mm
Width (a)	8.2 mm
Height	91.8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	gray
Flammability rating according to UL 94	V2
Material	PA

Standards and Regulations

Cover profile carrier - APH-ME - 3034374

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27141190

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC001041
ETIM 5.0	EC002848

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Dimensional drawing

