

Test adapter - PAI-4-FIX-5/6 BK - 3035980

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, for 4 mm Ø safety test plugs, latches into the bridge shaft; color: Black

The figure shows the version in orange

Product Features

- Make contact and latch securely to any point in the function shaft
- Test adapter for accommodating safety test plugs with a 4 mm diameter

Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	1.43 GRM
Custom tariff number	85366990
Country of origin	Poland

Technical data

Length	6.5 mm
Width	5.8 mm

General

Note	Touch proof against unintentional direct contact according to DIN EN 50274 when plugged in
	Do not plug in while the power is connected
Color	black

Maximum temperature	125 °C
---------------------	--------

Classifications

eCl@ss

eCl@ss 4.0	27141127
------------	----------

Test adapter - PAI-4-FIX-5/6 BK - 3035980

Classifications

eCl@ss

eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141111
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
