

## Spacer plate - DP PS-5 - 3036725

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Spacer plate, Length: 22.4 mm, Width: 5.2 mm, Height: 29 mm, Number of positions: 1, Color: red



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	1.5 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### General

Color	red
Material	PA
Flammability rating according to UL 94	V0

#### Dimensions

Width	5.2 mm
Length	22.4 mm
Height	29 mm

#### General

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Spacer plate - DP PS-5 - 3036725

### Classifications

#### eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141145
eCl@ss 5.1	27141145
eCl@ss 6.0	27141133
eCl@ss 7.0	27141133
eCl@ss 8.0	27141133
eCl@ss 9.0	27141133

#### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000886
ETIM 5.0	EC000886

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

### Drawings

# Spacer plate - DP PS-5 - 3036725

Dimensional drawing

