

## Fuse - FUSE 10,3X38 10A PV - 3061334

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse, 10.3x38 mm, up to 1000 V DC, gPV characteristics

### Product Features

- Use in PV lines with a nominal voltage of up to 1000 V DC

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	16.0 g
Custom tariff number	85361010
Country of origin	Slovenia

### Technical data

#### General

Color	white
Flammability rating according to UL 94	V0

#### Dimensions

Length	38 mm
Diameter	10.3 mm

#### General

Fuse	Midget / 10.3 x 38
Nominal current $I_N$	10 A
Nominal voltage $U_N$	1000 V AC/DC

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

# Fuse - FUSE 10,3X38 10A PV - 3061334

## Classifications

### eCl@ss

eCl@ss 4.0	27142001
eCl@ss 4.1	27142001
eCl@ss 5.0	27142001
eCl@ss 5.1	27142002
eCl@ss 6.0	27142002
eCl@ss 7.0	27142002
eCl@ss 8.0	27142002

### ETIM

ETIM 3.0	EC000035
ETIM 4.0	EC002704
ETIM 5.0	EC002704

### UNSPSC

UNSPSC 6.01	30211915
UNSPSC 7.0901	39121514
UNSPSC 11	39121514
UNSPSC 12.01	39121514
UNSPSC 13.2	39121514

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

---

