

Ferrule - A 6 -10 - 3202520

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ferrule, Length: 10 mm, Color: silver

The figure shows variant A 1-6

Product Features

- The A 0,25.. ferrules can also be used to process 0.14 mm² conductors
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Minimum order quantity | 500 pc |
| Weight per Piece (excluding packing) | 0.2 g |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--|--------|
| Length (b) | 10 mm |
| Maximum stripping length | 10 mm |
| Inner dimension of the insulating collar (d) | 4.7 mm |
| Ferrule diameter | 3.5 mm |
| Sleeve wall thickness | 0.2 mm |

Ambient conditions

| | |
|----------------------------|--------|
| Max. permanent temperature | 105 °C |
|----------------------------|--------|

General

| | |
|---------|-----------------------|
| Color | silver |
| Coating | tin-plated (galvanic) |

Standards and Regulations

Ferrule - A 6 -10 - 3202520

Technical data

Standards and Regulations

| | |
|----------------------------------|-----|
| Connection in acc. with standard | CSA |
|----------------------------------|-----|

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27060701 |
| eCl@ss 4.1 | 27060701 |
| eCl@ss 5.0 | 27400201 |
| eCl@ss 5.1 | 27400201 |
| eCl@ss 6.0 | 27400201 |
| eCl@ss 7.0 | 27400201 |
| eCl@ss 8.0 | 27400201 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000005 |
| ETIM 3.0 | EC000005 |
| ETIM 4.0 | EC000005 |
| ETIM 5.0 | EC000005 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |

Approvals

Approvals

Approvals

CSA / CSAus / EAC / EAC / cCSAus

Ex Approvals

Approvals submitted

Ferrule - A 6 -10 - 3202520

Approvals

Approval details

| |
|---|
| CSA  |
|---|

| |
|-------|
| CSAus |
|-------|

| |
|-----|
| EAC |
|-----|

| |
|-----|
| EAC |
|-----|

| |
|--------|
| cCSAus |
|--------|
