

Range box - AI SORTI BOX-E LGY - 3203008

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Range box, unequipped, color: light gray

Your advantages

- ✓ Color coding and the transparent cover facilitate fast access to the required ferrules
- ✓ The practical assortment boxes are designed to keep your workshop tidy
- ✓ Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 947156
GTIN	4017918947156
Weight per Piece (excluding packing)	75.970 g
Custom tariff number	39231090
Country of origin	Germany

Technical data

Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C (-40°C no load / 0°C dynamic load)

General

Color	light gray
Components	free from silicone and halogen
Flammability rating according to UL 94	HB

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Range box - AI SORTI BOX-E LGY - 3203008

Classifications

eCl@ss

eCl@ss 10.0.1	27400218
eCl@ss 4.0	27060700
eCl@ss 4.1	27060700
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	27400200
eCl@ss 7.0	27400218
eCl@ss 8.0	27400218
eCl@ss 9.0	27400218

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000524
ETIM 6.0	EC000524
ETIM 7.0	EC000524

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421