

Ferrule - AI 0,5-10 WH-GB - 3203150

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ferrule, Sleeve length: 10 mm, Length: 15.5 mm, Color: white

The illustration shows the version AI 0,5-10 WH

Why buy this product

- Due to the increased diameter of the insulating collar, this type of ferrule is specifically used with AWG cables
- These ferrules enable practical crimping of conductors with increased insulation

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 046356 135030
GTIN	4046356135030
Weight per Piece (excluding packing)	0.100 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Length (b)	15.5 mm
Maximum stripping length	13 mm
Sleeve length	10 mm
Inner dimension of the insulating collar (d)	3 mm
Ferrule diameter	1.1 mm
Insulating collar thickness	0.25 mm
Sleeve wall thickness	0.15 mm

Ambient conditions

Short-term temperature	120 °C
------------------------	--------

Ferrule - AI 0,5-10 WH-GB - 3203150

Technical data

Ambient conditions

Max. permanent temperature	105 °C
----------------------------	--------

General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	E-CU
Coating	tin-plated (galvanic)

Standards and Regulations

Connection in acc. with standard	CSA
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals

Approvals

CSA / CSAus / EAC / EAC / cCSAus

Ex Approvals

Approval details

CSA  http://www.csagroup.org/services/testing-and-certification/certified-product-listing/247397

CSAus http://www.csagroup.org/services/testing-and-certification/certified-product-listing/247397

EAC EAC-Zulassung

EAC 7500651.22.01.00246

Ferrule - AI 0,5-10 WH-GB - 3203150

Approvals

cCSAus <http://www.csagroup.org/us/en/services/testing-and-certification/certified-product-listing>

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>