

Cable duct - CD 30X100 WH - 3240623

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable duct for installation and mounting in control cabinets, white, comprising upper part and mounting base, width: 30 mm, height: 100 mm, length: 2000 mm

Your advantages

- ✓ Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- ✓ Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	12 pc
GTIN	 4 046356 629393
GTIN	4046356629393
Weight per Piece (excluding packing)	33.330 g
Custom tariff number	39259020
Country of origin	Germany

Technical data

Dimensions

Length (b)	2000 mm
Width (a)	30 mm
Height (c)	100 mm

Cable duct - CD 30X100 WH - 3240623

Technical data

Dimensions

Diameter	30.00 mm
----------	----------

Ambient conditions

Ambient temperature (operation)	-5 °C ... 60 °C
---------------------------------	-----------------

General

Color	white
Components	Lead-free
Flammability rating according to UL 94	V0
Material	PVC
Nominal cross section	1875 mm ²

Standards and Regulations

Halogen-free	no
Connection in acc. with standard	CSA
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27140600
eCl@ss 6.0	27400700
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703
eCl@ss 9.0	27400703

ETIM

ETIM 4.0	EC000012
ETIM 5.0	EC000012
ETIM 6.0	EC000012
ETIM 7.0	EC000012

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815

Cable duct - CD 30X100 WH - 3240623

Classifications

UNSPSC

UNSPSC 12.01	30101815
UNSPSC 13.2	39131712

Approvals

Approvals

Approvals

CSA / UL Recognized / VDE Zeichengenehmigung

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	248269
-----	--	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 328576
---------------	--	---	---------------

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx	40027969
------------------------	--	---	----------

Accessories

Accessories

Cover

Cover profile - CD COVER 30 WH - 3240646



Cover for cable duct, white, width: 30 mm, length: 2000 mm

Cable duct - CD 30X100 WH - 3240623

Accessories

Filler plug

Fastening clip - RVT-PA 4 - 3240498



Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm

Fastening clip - RVT-PA 6 - 3240499



Plastic body-bound rivet, for hole diameter of 6 mm and a material thickness of 1.5 ... 6 mm

Riveting tools

Tool - UNIFOX-RVT P 4 - 1212478



Rivet setting tool, for use with RVT-PA 4 plastic body-bound rivets

Tool - UNIFOX-RVT P 6 - 1212509



Rivet setting tool, for use with RVT-PA 6 plastic body-bound rivets

Wiring duct

Cable duct - CD 30X100 WH - 3240623

Accessories

Universal wire retaining clip - CD WR - 3240284



Universal wire holding bracket, perforated, for wiring channels
