

Cover profile - CD COVER 30 WH - 3240646

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover for cable duct, white, width: 30 mm, length: 2000 mm



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 046356 629720
GTIN	4046356629720
Custom tariff number	39259020
Country of origin	Germany

Technical data

Dimensions

Length (b)	2000 mm
Width (a)	30 mm
Height	14.4 mm

Ambient conditions

Ambient temperature (operation)	-5 °C ... 60 °C
---------------------------------	-----------------

General

Color	white
Components	Lead-free
Flammability rating according to UL 94	V0
Material	PVC

Cover profile - CD COVER 30 WH - 3240646

Technical data

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400776
eCl@ss 8.0	27400776
eCl@ss 9.0	27400776

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000727
ETIM 4.0	EC000727
ETIM 5.0	EC000727
ETIM 6.0	EC000727

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	39131712