

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	360.0 g
Custom tariff number	96121020
Country of origin	Japan

Technical data

Dimensions

Length (b)	300.00 m
Width (a)	110.00 mm

Ambient conditions

Recommended storage conditions	5-35 °C / 30-85 % relative humidity.
--------------------------------	--------------------------------------

General

Color	black
-------	-------

Classifications

eCl@ss

eCl@ss 4.0	24190105
eCl@ss 4.1	24190105
eCl@ss 5.0	19029102
eCl@ss 5.1	19029102
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	19149290

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001675
ETIM 5.0	EC001675

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107