


## Socket - EM-DUO 120/15/GFIV/H - 5604775

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



### Key commercial data

Packing unit	1 PCE
Minimum order quantity	10 PCE
GTIN	 4 046356 687577
Country of origin	UNITED STATES

### Technical data

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

#### General

Nominal voltage $U_N$	125 V AC
Nominal current $I_N$	15 A
Insulating material	PVC 94 V0
Standards/regulations	UL 508

#### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	6 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	30
Conductor cross section AWG/kcmil max	10
Connection method	Screw connection
Stripping length	8 mm

## Socket - EM-DUO 120/15/GFIV/H - 5604775

### Technical data

#### Connection data

Screw thread	M3
--------------	----

### Classifications

#### ETIM

ETIM 3.0	EC001325
ETIM 4.0	EC001325
ETIM 5.0	EC001325

#### UNSPSC

UNSPSC 11	39121406
UNSPSC 12.01	39121406
UNSPSC 13.2	39121406
UNSPSC 6.01	30211806
UNSPSC 7.0901	39121406

#### eCl@ss

eCl@ss 4.0	27142305
eCl@ss 4.1	27142305
eCl@ss 5.0	27143412
eCl@ss 5.1	27143412
eCl@ss 6.0	27143412
eCl@ss 7.0	27440519