

## Flange cover - DF-UP 4 - 3060348

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Flange cover, Length: 47 mm, Width: 4.5 mm, Height: 24.7 mm, Color: gray

screw version

### Product Description

snap onto the UP 4/... plugs

### Why buy this product

- For reliable screw connection between the plug and screw flange
- The flange covers can be snapped onto the plug housing later on

### Key Commercial Data

|              |   |
|--------------|---|
| Packing unit | 50 STK  |
| GTIN         | <br>4 046356 091633 |

### Technical data

#### General

|   |        |
|---|--------|
| Color   | gray   |
| Material  | PA     |
| Flammability rating according to UL 94                                  | V0     |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Static insulating material application in cold                          | -60 °C |

#### Dimensions

|        |         |
|--------|---------|
| Width  | 4.5 mm  |
| Length | 47 mm   |
| Height | 24.7 mm |

#### Connection data

|                        |        |
|------------------------|--------|
| Tightening torque, min | 0.4 Nm |
| Tightening torque max  | 0.5 Nm |

#### Standards and Regulations

# Flange cover - DF-UP 4 - 3060348

## Technical data

### Standards and Regulations

|  |    |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141199 |
| eCl@ss 4.1 | 27141199 |
| eCl@ss 5.0 | 27141145 |
| eCl@ss 5.1 | 27141145 |
| eCl@ss 6.0 | 27141133 |
| eCl@ss 7.0 | 27141133 |
| eCl@ss 8.0 | 27141133 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000886 |
| ETIM 3.0 | EC000886 |
| ETIM 4.0 | EC000886 |
| ETIM 5.0 | EC000886 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211827 |
| UNSPSC 7.0901 | 39121424 |
| UNSPSC 11     | 39121424 |
| UNSPSC 12.01  | 39121424 |
| UNSPSC 13.2   | 39121424 |

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>