

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Thermal transfer printer, 300 dpi, incl. European power cable, US power cable, and USB cable. DVD with CLIP PROJECT advanced planning and marking software, user manuals in various languages, Windows® printer driver, and firmware. German/English user manual in DIN A5 format, EML (20x8)R roll of labels, white, with 1000 labels, and ink ribbon: 50 m

### Why buy this product

- ✓ The THERMOMARK ROLLMASTER 300 is an industrial printer for printing large quantities of marking materials in roll format. Print resolution of 300 dpi.
- ✓ Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- ✓ Fast, high-quality, and durable printing
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and intuitive operation via touch color display
- ✓ Easy and flexible control by means of the multilingual CLIP PROJECT planning and marking software. With the option of direct entry or import of printing information from various data sources
- ✓ USB and Ethernet connections

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 381619
GTIN	4055626381619
Custom tariff number	84433210
Country of origin	Germany

### Technical data

#### General

Interface	10/100 Mbps Ethernet
	USB 2.0
Weight	10 kg

# Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

## Technical data

### Dimensions

Length	460 mm
Height	288 mm
Width	380 mm

### Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Classifications

### eCl@ss

eCl@ss 4.0	24190103
eCl@ss 4.1	24190103
eCl@ss 5.0	19020205
eCl@ss 5.1	19020205
eCl@ss 8.0	19140104
eCl@ss 9.0	19140104

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 6.0	EC001672

### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212107

## Approvals

### Approvals

# Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

## Approvals

### Approvals

UL Listed / cUL Listed / EAC / CCC / cULus Listed

---

### Ex Approvals

---

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140403
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140403
------------	--	---	---------------

EAC			RU *- DE.A*30.B.02513
-----	--	--	--------------------------

CCC		<a href="http://www.china-certification.com">http://www.china-certification.com</a>	2018010904060718
-----	--	---	------------------

cULus Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	
--------------	--	---	--

## Accessories

### Accessories

#### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, for roll printer for printing product groups TML..., WML..., WML HF..., WML-FLAG..., WMT..., WMTB..., EML..., EML-ESD..., EML-RM..., EML-HA..., EMLS..., EMLC..., EMLP..., EMLF..., PML..., and PMM..., width: 110 mm, color: black

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

### Accessories

Ink ribbon - THERMOMARK-RIBBON 110 BU - 0829544



Ink ribbon, width: 110 mm, color: blue

---

Ink ribbon - THERMOMARK-RIBBON 110 GN - 0829542



Ink ribbon, width: 110 mm, color: green

---

Ink ribbon - THERMOMARK-RIBBON 110 RD - 0829543



Ink ribbon, width: 110 mm, color: red

---

Ink ribbon - THERMOMARK-RIBBON 110-EML-HT - 0800342



Ink ribbon, for roll printer for printing product group EML-HT..., width: 110 mm, color: black

---

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

---

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

### Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU WH - 0801359



Ink ribbon, for roll printer for printing product group WMS... (black), width: 110 mm, color: white

---

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

---

Ink ribbon - THERMOMARK-RIBBON 64-WMSU WH - 0801361



Ink ribbon, for roll printer for printing product group WMS... (black), width: 64 mm, color: white

---

Ink ribbon - THERMOMARK-RIBBON 110-WMTB HF - 5148007



Ink ribbon, for roll printer for printing product groups WMTB HF..., WMS-2 HF..., TMT..., and EMT..., width: 110 mm, color: black

---

Ink ribbon - TM-RIBBON 110-WMTB HF WH - 0802990



Ink ribbon, for roll printer for printing product group WMTB HF..., width: 110 mm, color: white

---

### Planning and marking software

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

### Accessories

Software - CLIP-PROJECT ADVANCED - 5146040



Multilingual software for convenient configuration of Phoenix Contact products on standard DIN rails.

---

Software - CLIP-PROJECT PROFESSIONAL - 5146053



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

---

### Printing system accessories

Cutter - THERMOMARK ROLLMASTER-CUTTER - 0804502



Cutter

---

Cutter - THERMOMARK ROLLMASTER-CUTTER/P - 0804503



Cutter

---

Screw - TRM-ADAPTER SCREW - 0804653



Adapter screw for using the existing THERMOMARK X1.2 CUTTER and THERMOMARK X1.2 CUTTER/P

---

# Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

## Accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

---

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

---

Pressure roller - TRM-PRESSURE ROLLER STANDARD - 0804655



Standard pressure roller

---

Pressure roller - TRM-PRESSURE ROLLER 4-50 - 0804656



Pressure roller for continuous shrink sleeve

---

Case - THERMOMARK ROLLMASTER-CASE - 0804643



Transport case for THERMOMARK ROLLMASTER printer

---

## Thermal transfer printer - THERMOMARK ROLLMASTER 300 - 0804501

### Accessories

Cleaning pen - CLEANING STICK - 5146697



Cleaning pen

---

Pressure roller - TRM-MARGIN STOP - 0804657



Pressure roller

---

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

---

Media hub - THERMOMARK-ERH 500 - 5146309



External media hub, for the THERMOMARK ROLL, for roll diameter of up to 500 mm

---