

DC/DC converters - UNO-PS/350-900DC/24DC/60W - 2906300

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Primary-switched UNO DC/DC converter with wide range input, for DIN rail mounting, input: 350 ... 900 V DC, output: 24 V DC/60 W

Product Description

UNO DC/DC converters with basic functionality


With the DC/DC converters from the UNO POWER range, the control cabinet is supplied directly from the photovoltaic system. This saves installation costs and increases the efficiency of the system.

Why buy this product

- Wide input voltage range
- Direct field installation
- UL 1741-certified DC/DC converter
- Minimal space required in the control box
- Simplified startup



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 062648
GTIN	4055626062648
Weight per Piece (excluding packing)	320.000 g
Custom tariff number	85044030
Country of origin	Germany