


SWITCHES STANDARD TOGGLE

HEAVY DUTY TOGGLE SWITCHES, AC/DC MOTOR CONTROL



Mounting Hole: 0.500"

SPECIFICATIONS:

Current Rating: 16A @ 125V AC, 8A @ 250V AC
1 HP @ 125-250V AC

Insulation Resistance: 100 Meg ohm (Min.)

Dielectric Strength: 1000V 1 minute

Base Material: Phenolic

Bezel Material: Brass/Nickel Plate


Terminal Type: .Screw (#6-32NC-2 Thread)

Part No.	Type	Action		Actuator
30-10341	SPST	ON	OFF	Brass Nickel Plate
30-10131	DPST	ON	OFF	Brass Nickel Plate
30-10342*	DPST	ON	OFF	Brass Nickel Plate

* = Rating for 30-10342 is 20A @ 125VAC, 10A @ 250VAC, 1-1/2 HP 125-250VAC



STANDARD SIZE BAT HANDLE TOGGLE SWITCH



Mounting Hole: 0.500"

SPECIFICATIONS:

Current Rating: 15A @ 125V AC, 10A @ 277V AC

Initial Contact Resistance: 50 Meg ohm (Max.)

Insulation Resistance: 100 Meg ohm (Min.) @ 500V DC

Dielectric Strength: 1000V AC 50/60 Hz for 1 minute

Contact Material: Brass - Silver Plate

Terminal Material: Brass


Terminal Type: Screw

Part No.	Type	Action		Actuator
30-067	SPST	ON	OFF	Metal
30-10360*	DPST	ON	OFF	Metal

* = 3/4 HP 125-250VAC



STANDARD SIZE BAT HANDLE TOGGLE SWITCHES



SPECIFICATIONS:

Current Rating: 20A @ 125V AC, 10A @ 277V AC
3/4 HP @ 125/277V AC
*1-1/2 HP @ 125/277V AC

Initial Contact Resistance: 50 Meg ohm (Max.)

Insulation Resistance: 100 Meg ohm (Min.) @ 500V DC

Dielectric Strength: 1000V AC 50/60 Hz for 1 minute

Contact Material: Brass - Nickel Plate


Terminal Material: Brass

Terminal Type: Screw

Part No.	Type	Action		Actuator
30-020*	SPST	ON	OFF	Metal
30-022	SPDT	ON	ON	Metal



STANDARD SIZE BAT HANDLE TOGGLE SWITCHES



SPECIFICATIONS:

Current Rating: 6A @ 125V AC, 3A @ 277V AC

Initial Contact Resistance: 50 Meg ohm (Max.)

Insulation Resistance: 100 Meg ohm (Min.) @ 500V DC

Dielectric Strength: 1000V AC 50/60 Hz for 1 minute

Contact Material: Brass - Nickel Plate

Terminal Material: Brass

Terminal Type: .250" Quick Connect

Part No.	Type	Action	Actuator	
30-019	DPST	ON	OFF	Metal

